






ROHS

RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

Specification:

1.Material:

Insulator:HI-Temp Plastic UL 94V-O Rated

Contact:Copper Alloy($t=0.15\text{mm}$)Shell:Stainless Steel($t=0.15\text{mm}$)

Spring:SWP

2.Electrical Characteristics:

Contact Current Rating:0.5 Amperes.

Dielectric Withstanding Voltage:AC500V r.m.s.

Insulation Resistance:1000 MΩ Minimum.

Contact Resistance:40 mΩ Maximum.

3.Environmental:

Operating Temperature: $-25^{\circ}\text{C}\sim+90^{\circ}\text{C}$.

4.Environmental:

Mating Cycles:5,000 Insertions.

PIN NO.	NAME	YYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATO	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

06/07-18	Zhang		NEW-DWG		A0
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.
UNLESS OTHERWISE SPECIFIED TOLERANCES		深圳市辉焕科技有限公司			
			TITLE: TF-CARD 01		
X. ±0.30	X.XXX ±0.10	APPD:	PRODUCT NO:		
X.X ±0.25	X.X* ±3.00	CHECK:	DATE	SCALE	UNIT TYPE PAGE
X.XX ±0.15	X.XX* ±1.00	DRAW:	2018.03.03	1:1	mm CD 2/1

