






REV. (版本号)	DESCRIPTION (变更说明)	DATE (日期)	APPO (签名)



规格说明 Specifications:

电气特性 Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
 - 2.额定电压: Voltage Rating
30V DC
 - 3.接触电阻 Contact Resistance
30 milliohms MAX
 - 4.耐电弧 Dielectric Withstanding Voltage
500 V AC AT Sea Level
 - 5.绝缘强度 Insulation Resistance:
1000MΩ ohms MIN

原材料 Raw material:

1. 膠: Plastic cement:
Hing Temperature Thermoplastics,
PBT White/Black
 2. 塗: Contact: Copper Alloy C2680

3.4.3 由條目

- ① 端子 Contact: Plated Gold in Mating Area
Tin On Solder Tails

② 外壳 Shell:
Nickel Plating

浙江创都电子科技有限公司

浙江创都电子科技有限公司		页码 (SHEET)	1/1	单位 (UNIT): MM
版本 (REV)		A/2	比例 (SCALE) 1:1	
日期 (DATE)		2011.06.18		
品名 (ITEM NO)	USB2.0-BF-WJ-CU	设计 (DESIGN)		未注公差 TOLERANCE UNSPECIFIED
料号 (PART NO)		审核 (CHECKED)		X.X ±0.10 X.XX ±0.20 X.XXX ±0.10
图号 (DWG NO)		被准 (APPROVED)		X* ±5° X.X* ±2°