




规格书: Specifications:

电气特性: Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触电阻: Contact Resistance
30 milliohms MAX
- 耐压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

原材料: Raw material:

- 塑胶: Plastic cement:
King Temperature Thermoplastics,
PBT White/Black
- 端子: Contact: Copper Alloy C2680
- 外壳: Shell: SPCC/Copper Alloy C2680

电镀: Electroplate:

- 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
- 外壳: Shell:
Nickel Plating

浙江创都电子科技有限公司

品名 (ITEM NO) USB2.0-BF-WJ-BK-CU

料号 (PART NO)

图号 (DWG NO)

页码 (SHEET)	1/1	单位 (UNIT):	MM
版本 (REV)	A/2	比例 (SCALE)	1:1
日期 (DATE)	2011.06.18		
设计 (DESIGN)	未注公差 TOLERANCE UNSPECIFIED		
审核 (CHECKED)	X.X ±0.30 X.XX ±0.20 X.XXX ±0.10		
批准 (APPROVED)	X" ±5" X.X" ±2"		