







REV	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		



1. FPC NOT MATING CONDITION BANNED CLOSURE
2. ALL MATERIAL MUST BE COMPLY WITH ROHS

- ① .SERIES NAME:F604=FPC 1.0PITCH H2.0 BACK FLIP TYPE CONNECTOR
- ② .CONTACT PIN NUMBER:**=CONTACT PIN NUMBER
- ③ .WELDING METHODS:1=SMT
- ④ .SHELLS MATERIALS/PLATING:X=MEANINGLESS CODE
- ⑤ .MAIN COLOR:3=NATURAL COLOR
- ⑥ .CONTACT PLATING SPEC:
POINT OF PLATING: $30=1u''$;
ALL GOLD PLATING: $20=1u''$; $22=3u''$; $23=5u''$;
TIN PLATING;06=ALL MATTE TIN
- ⑦ .PACKING SPEC: 3=CARRY TAPE



NO.	COMPONENTS	MATERIALS	COLOR/SPECIFICATION	QUANTITY
1	HOUSING	LCP	NATURAL UL94V-0	1 PCS
2	COVER	PA9T	BLACK UL94V-0	1 PCS
3	CONTACT	PHOSPHOR BRONZE	T=0.15mm PLATING	POSITIONS
4	STATOR	BRASS	T=0.15mm PLATING	2 PCS

DESIGN:		Xiping Huang			广东国连电子有限公司				
CHECK:		Ke Tian			GUANGDONG GUOLIAN ELECTRONICS CO., LTD				
APPROVED:		Youquan Xu			TITLE:				
DIM		TOL	DIM	TOL	1.0前插后掀H2.0				
X.		±0.25	X°	±3.0°	PART NO.				
X.X		±0.20	X.X°		1020-GX-NPWB-***				
X.XX		±0.15	X.XX°		REV. A				
X.XXX			X.XXX°		SCALE:	N/A	UNIT:	SHEET:	
							mm	1/1	