







RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK	Yang	151006
	新增图档				190604



P.C.B LAYOUT
TOLERANCE: ± 0.05



备注:

- 额定电流: 5.0A (单PIN);
- 额定电压: AC/DC 30V Max
- 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
- 绝缘电阻: DC 500V 1 MINUTE, 1000M Ω Min
- 操作温度: -40° to +85°
- 塑胶材质: LCP/PA9T黑色/耐高温260° $\pm 5^\circ$,
- 五金材质: 黄铜(T=0.6mm)/镀金1u"

Table:

PART NUMBER	P / N	Dim. A	Dim. B	Dim. C
JME2Mxx-H053001TZ-B	03pin	6.50	5.90	4.00
JME2Mxx-H053001TZ-B	04pin	8.50	7.90	6.00
JME2Mxx-H053001TZ-B	05pin	10.50	9.90	8.00
JME2Mxx-H053001TZ-B	06pin	12.50	11.90	10.00
JME2Mxx-H053001TZ-B	07pin	14.50	13.90	12.00
JME2Mxx-H053001TZ-B	08pin	16.50	15.90	14.00

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司
	MM	INCH	MATERIAL:	HRC:	
∇^0 ∇^C	.X ± 0.25	.X @	DRAWN BY JK-YANG	DATE	TITLE: Battery 2.0PH 5.3H SMT 有柱 公座
	.XX ± 0.15	.XX @	CHECKED BY	DATE	
	.XXX ± 0.05	.XXX @	APPROVED BY	DATE	THIRD ANGLE PROJECTION
ANGULAR $\pm 1^\circ$			REVISE ON CAD ONLY		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			PART NO. JME2Mxx-H053001TZ-B	DWG. NO.	SHEET NO. 1/1