

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK	Yang	150515

A

B

C

D

E

F

A




B

C

D

E

F



P.C.B LAYOUT
TOLERANCE: ±0.05

Table:

PART NUMBER	P / N	Dim. A	Dim. B	Dim. C
JME2Mxx-H053001AZ-B	02pin	4.50	3.90	2.00
JME2Mxx-H053001AZ-B	03pin	6.50	5.90	4.00
JME2Mxx-H053001AZ-B	04pin	8.50	7.90	6.00
JME2Mxx-H053001AZ-B	05pin	10.50	9.90	8.00
JME2Mxx-H053001AZ-B	06pin	12.50	11.90	10.00
JME2Mxx-H053001AZ-B	07pin	14.50	13.90	12.00
JME2Mxx-H053001AZ-B	08pin	16.50	15.90	14.00

备注:

- 额定电流: 5.0A (单PIN);
- 额定电压: AC/DC 30V Max
- 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
- 绝缘电阻: DC 500V 1 MINUTE, 1000MΩ Min
- 操作温度: -40° to +85°
- 塑胶材质: LCP/PA9T 黑色/耐高温260° ±5° ,
- 五金材质: 黄铜 (T=0.6mm) /镀金1u"

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司								
		MM		INCH		MATERIAL:		HRC:										
 0	.X	±0.25		.X	Ⓢ	DRAWN BY JK-YANG		DATE		TITLE: Battery 2.0PH 5.3H DIP 公座								
	.XX	±0.15		.XX	Ⓢ													
		.XXX	±0.05		.XXX	Ⓢ	CHECKED BY		DATE		 THIRD ANGLE PROJECTION				REVISE ON CAD ONLY			
ANGULAR ±1°																		
 0	DRAFT WHERE APPLICABLE						APPROVED BY		DATE		PART NO. JME2Mxx-H053001AZ-B		DWG NO.		SHEET NO. 1/1		A	
MUST REMAIN WITHIN DIMENSIONS																		

A4