

MATERIAL




1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD FLASH PLATING OVER NICKEL.
4. SHIELD: BRASS T0.20mm 40u" NICKEL PLATED.
ELECTRICAL
1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC
RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL



1.DURRABILITY: 750 CYCLES MIN.
2.MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

1.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.



8	—
7	—
6	RX—
5	—
4	—
3	RX+
2	TX—
1	TX+
PIN	说明



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.35	X.*±3	APR. Alex	TITLE: RJ45 56B塑壳 塑料连接器 DIP			
.XX±0.25	.X*±2	CHK. Jack	DWG NO. XY-RJ45R08PC			
.XXX±0.15	.XX*±1	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A