

RoHS
Compliant

结构图面

Material

Insulator:Nylon 9T(UL94V-0)

TERMINAL:phosphor Bronze

TERMINAL Plated:Gold over Nickel

or Tin

Specification

Current rating:7A





instant CURRENT:10A

Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°



Recommended P.C.B Layout

Layout Tolerance=+/-0.05mm

PARTNUMBER	No. of Pins	Dimension	
		DIM. A	DIM. B
JME25Mxx-H042001B-B	02	7.00	2.50
JME25Mxx-H042001B-B	03	9.50	5.00
JME25Mxx-H042001B-B	04	12.00	7.50
JME25Mxx-H042001B-B	05	14.50	10.00
JME25Mxx-H042001B-B	06	17.00	12.50
JME25Mxx-H042001B-B	07	19.50	15.00
JME25Mxx-H042001B-B	08	22.00	17.50
JME25Mxx-H042001B-B	09	24.50	20.00
JME25Mxx-H042001B-B	10	27.00	22.50
JME25Mxx-H042001B-B	11	29.50	25.00
JME25Mxx-H042001B-B	12	32.00	27.50
JME25Mxx-H042001B-B	13	34.50	30.00
JME25Mxx-H042001B-B	14	37.00	32.50
JME25Mxx-H042001B-B	15	39.50	35.00
JME25Mxx-H042001B-B	16	42.00	37.50

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司			
			MM		INCH	MATERIAL:		HRC:					
 0		.X	±0.25	.X	Ⓢ	DRAWN BY		DATE		TITLE: Battery 2.5PH 90度DIP 4.2H 公			
		.XX	±0.15	.XX	Ⓢ								
			.XXX	±0.05	.XXX	Ⓢ	CHECKED BY		DATE				
 0	ANGULAR ±1°					APPROVED BY					DATE		 THIRD ANGLE PROJECTION
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
						PART NO.		JME25Mxx-H042001B-B		DWG NO.		SHEET NO. 1/1	