











适用扁平线(Applicable Flat Cable)

适用线路板(PCB LAYOUT)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~+85°C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

序号	品名	材质
1	1.0插头(H2.5)	LCP UL94V-0 本色
2	1.0下端子(H2.5)	铜合金/表面镀锡
3	1.0卧式后盖(H2.5)	LCP UL94V-0 黑色
4	1.0卧式垫片(H2.5)	铜合金/表面镀锡

Part No	Pfn	A	B	C
XY-FPC-10-CTD-4RLTAG	4	3.00	5.03	11.10
XY-FPC-10-CTD-5RLTAG	5	4.00	6.03	12.10
XY-FPC-10-CTD-6RLTAG	6	5.00	7.03	13.10
XY-FPC-10-CTD-7RLTAG	7	6.00	8.03	14.10
XY-FPC-10-CTD-8RLTAG	8	7.00	9.03	15.10
XY-FPC-10-CTD-9RLTAG	9	8.00	10.03	16.10
XY-FPC-10-CTD-10RLTAG	10	9.00	11.03	17.10
XY-FPC-10-CTD-11RLTAG	11	10.00	12.03	18.10
XY-FPC-10-CTD-12RLTAG	12	11.00	13.03	19.10
.....		...		
XY-FPC-10-CTD-40RLTAG	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+8)*1.0+0.10

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR. Alex	TITLE: 1.0 Pitch H2.5 ZIF R/A Type Under CONN		
.XX±0.25	.X.*± 3°	CHK. Jack	DWG NO. XY-FPC-10-CTD-NRLTAG		
.XXX±0.15	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1