




SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40°to+105°
Insulator Material: Polyester(UL94V-0)
Contact Material: Brass
Standard: PA6T
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ127V-11-01P-0720	1	0.00	1.27
XY-PZ127V-11-02P-0720	2	1.27	2.54
XY-PZ127V-11-03P-0720	3	2.54	3.81
XY-PZ127V-11-04P-0720	4	3.81	5.08
XY-PZ127V-11-05P-0720	5	5.08	6.35
XY-PZ127V-11-06P-0720	6	6.35	7.62
XY-PZ127V-11-07P-0720	7	7.62	8.89
XY-PZ127V-11-08P-0720	8	8.89	10.16
XY-PZ127V-11-09P-0720	9	10.16	11.43
.....			
XY-PZ127V-11-50P-0720	50	(PIN-1)x1.27	(PIN)x1.27



DIMENSION in mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.35	X.*± 5°	APR.	Alex	TITLE: 1.27PH H1.0 1xnPin 180 W2.0 PC2.3 PA3.9 PB1.0 L7.2 6T 0.4#		
.XX±0.2	.X*± 1	CHK.	Jack	DWG NO. XY-PZ127V-11-04P-0720		
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ. 		CUSTOMER DRAWING
				SIZE A4	SCALE 1:1	SHEET 1/1