





RoHS  
Compliant

结构图面

| REV | DESCRIPTION | APPR | CHECK | DRAW | DATE   |
|-----|-------------|------|-------|------|--------|
| △0  | 原始图档        |      | JACK  |      | 120606 |

Material  
Insulator:Nylon 9T(UL94V-0)  
TERMINAL:phosphor Bronze  
TERMINAL Plated:Gold over Nickel  
or Tin  
Specification  
Current rating:7A  
instant CURRENT:10A  
Contact Resistance:30MΩ  
Insulation Resistance:100MΩ  
Dielectric Voltage:500V  
Operdting Temperature:-40°~105°

| No. of Pins | Dimension |        |
|-------------|-----------|--------|
|             | DIM. B    | DIM. A |
| 02          | 7.00      | 2.50   |
| 03          | 9.50      | 5.00   |
| 04          | 12.00     | 7.50   |
| 05          | 14.50     | 10.00  |
| 06          | 17.00     | 12.50  |
| 07          | 19.50     | 15.00  |
| 08          | 22.00     | 17.50  |
| 09          | 24.50     | 20.00  |
| 10          | 27.00     | 22.50  |
| 11          | 29.50     | 25.00  |
| 12          | 32.00     | 27.50  |
| 13          | 34.50     | 30.00  |
| 14          | 37.00     | 32.50  |
| 15          | 39.50     | 35.00  |
| 16          | 42.00     | 37.50  |



Recommended P.C.B Layout  
Layout Tolerance=+/-0.05mm

| QUALITY SYMBOLS | GENERAL TOLERANCES (UNLESS SPECIFIED)                |       |      |      | SCALE: 1:1  | NUMBER: | 东莞市文章济美电子有限公司                       |               |
|-----------------|------------------------------------------------------|-------|------|------|-------------|---------|-------------------------------------|---------------|
|                 |                                                      | MM    |      | INCH | MATERIAL:   | HRC:    | TITLE: Battery 2.5PH 90度DIP 5.8H 公座 |               |
| ▽0              | .X                                                   | ±0.25 | .X   | ②    | DRAWN BY    | DATE    | THIRD ANGLE PROJECTION              |               |
|                 | .XX                                                  | ±0.15 | .XX  | ②    | CHECKED BY  | DATE    | REVISE ON CAD ONLY                  |               |
|                 | .XXX                                                 | ±0.05 | .XXX | ②    | APPROVED BY | DATE    | PART NO. JME25Mxx-H058001B-B        | SHEET NO. 1/1 |
| ▽C0             | ANGULAR ±1°                                          |       |      |      |             |         |                                     |               |
|                 | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |       |      |      |             |         |                                     |               |