

SPECIFICATIONS

Current Rating:1.0 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:-40° to+105°

Insulator Material:Polyester(UL94V-0)





Contact Material:Brass

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ127VS-12-01P-H10-P38	2*1	0.00	1.27
XY-PZ127VS-12-02P-H10-P38	2*2	1.27	2.54
XY-PZ127VS-12-03P-H10-P38	2*3	2.54	3.81
XY-PZ127VS-12-04P-H10-P38	2*4	3.81	5.08
XY-PZ127VS-12-05P-H10-P38	2*5	5.08	6.35
XY-PZ127VS-12-06P-H10-P38	2*6	6.35	7.62
XY-PZ127VS-12-07P-H10-P38	2*7	7.62	8.89
XY-PZ127VS-12-08P-H10-P38	2*8	8.89	10.16
XY-PZ127VS-12-09P-H10-P38	2*9	10.16	11.43
.....			
XY-PZ127VS-12-50P-H10-P38	2*50	(PIN-1)x1.27	(PIN)x1.27

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR. Alex	TITLE: 1.27PH H1.0 2xnPin SMT W3.4 PC5.5 PA4.0 PB1.5 L7.2 6T		
.XX±0.2	.X.*± 1	CHK. Jack	DWG NO. XY-PZ127VS-12-10P-H10-P38		
.XXX±0.1	.XX.*± 0.5	DRA. Can	PROJ.	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		