

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
0	变更图档		JACK	Yang	220707

- 备注:
1. 额定电流: 5.0A (单PIN);
 2. 额定电压: AC/DC 30V Max
 3. 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
 4. 绝缘电阻: DC 500V 1 MINUTE, 1000M Ω Min
 5. 操作温度: -40° to +85°
 6. 塑胶材质: LCP/PA9T黑色/耐高温260° $\pm$ 5° ,
 7. 五金材质: 黄铜(T=0.6mm)/镀金1u"

Table

PART NUMBER	PIN	Dim. A	Dim. B
JME2Mxx-H026001BC-B	02pin	4.50	2.00
JME2Mxx-H026001BC-B	03pin	6.50	4.00
JME2Mxx-H026001BC-B	04pin	8.50	6.00
JME2Mxx-H026001BC-B	05pin	10.50	8.00
JME2Mxx-H026001BC-B	06pin	12.50	10.00
JME2Mxx-H026001BC-B	07pin	14.50	12.00
JME2Mxx-H026001BC-B	08pin	16.50	14.00

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司				
▽₀		MM		INCH	MATERIAL:	HRC:	TITLE: MINI 2.0PH 90度DIP沉板式 公座					
	. X	±0.25	. X	Ⓜ	DRAWN BY	DATE						
	. XX	±0.15	. XX	Ⓜ	JK-YANG		⌀ Ⓜ THIRD ANGLE PROJECTION REVISE ON CAD ONLY					
	. XXX	±0.05	. XXX	Ⓜ	CHECKED BY	DATE						
▽_C	ANGULAR ±1°				APPROVED BY	DATE	PART NO.	JME2Mxx-H026001BC-B		DWG NO.	SHEET NO. 1/1	A4
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											