



REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40℃ to +105℃

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PA6T+30%GF(UL94V-0)





Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

MTP125-12XXM2

No.of Pins per
 Row: 01~40



Dimension antitheses list			
ITEM	D	B	W
Standard	0.60	6.00	7.50
Alternate			

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.									
.X ± 0.20	.X° ± 2°	MAT'L											
.XX ± 0.10	.XX° ± 1°	FINISH	PART NO.(INTENDED USE)	TITLE:									
.XXX ± 0.05	.XXX° ± 0.5°		APPD: SUNNY	PIN HEADER 2.54 DUAL ROW SMT H=2.5									
PIN HEADER CONNECTOR		Q'TY	CHKD: LISA	DWG NO.: MTP125-12XXM2									
			DR: ZOE 2006-11-28	 <table><tr><th>SCALE</th><th>SHEET</th><th>REV.</th></tr><tr><td>1 / 1</td><td>1 / 1</td><td>A</td></tr></table>				SCALE	SHEET	REV.	1 / 1	1 / 1	A
			SCALE					SHEET	REV.				
1 / 1	1 / 1	A											