





RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	新增图档		JACK	Yang	1801018



备注:

- 材料: LCP黑色, 黄铜镀金;
- 额定电压: AC/DC 30V Max
- 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
- 绝缘电阻: DC 500V 1 MINUTE, 1000MΩ Min
- 操作温度: -20° to +80°
- Current rating: 5A
- instant CURRENT: 7A

Table

PART NUMBER	PIN	Dim. A	Dim. B	Dim. C
JME2Mxx-H026001BZ-B	02pin	4.50	3.90	2.00
JME2Mxx-H026001BZ-B	03pin	6.50	5.90	4.00
JME2Mxx-H026001BZ-B	04pin	8.50	7.90	6.00
JME2Mxx-H026001BZ-B	05pin	10.50	9.90	8.00
JME2Mxx-H026001BZ-B	06pin	12.50	11.90	10.00
JME2Mxx-H026001BZ-B	07pin	14.50	13.90	12.00
JME2Mxx-H026001BZ-B	08pin	16.50	15.90	14.00
JME2Mxx-H026001BZ-B	09pin	18.50	17.90	16.00
JME2Mxx-H026001BZ-B	10pin	20.50	19.90	18.00

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司											
			MM		INCH	MATERIAL:		HRC:													
▽ 0		.X	±0.25	.X	⑩	DRAWN BY JK-YANG		DATE		TITLE: MINI 2.0PH 90度DIP 2.6H 公座											
		.XX	±0.15	.XX	⑩																
			.XXX	±0.05	.XXX	⑩	CHECKED BY		DATE												
C 0		ANGULAR ±1°				APPROVED BY					DATE		PART NO. JME2Mxx-H026001BZ-B		THIRD ANGLE PROJECTION		REVISE ON CAD ONLY		DWG NO.		SHEET NO. 1/1
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																			