



RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK	Yang	150518

NOTE:
Material
Insulator:Nylon 9T(UL94V-0)
Contact:phosphor Bronze
Contact Plated:Gold over Nickel
or Tin Specification,全金1U
Current rating:7A
instant CURRENT:10A
Contact Resistance:30MΩ
Insulation Resistance:100MΩ
Dielectric Voltage:500V
Operdting Temperature:-40°~105°



No. of Pins	Dimension		
	DIM. A	DIM. B	DIM. C
03	11.65	4.00	9.15
04	13.65	6.00	11.15
05	15.65	8.00	13.15
06	17.65	10.00	15.15
07	19.65	12.00	17.15
08	21.65	14.00	19.15
09	23.65	16.00	21.15
10	25.65	18.00	23.15
11	27.65	20.00	25.15
12	29.65	22.00	27.15
13	31.65	24.00	29.15
14	33.65	26.00	31.15
15	35.65	28.00	33.15

RECOMMENDED PCB LAYOUT
T=1.2MM,TOLERANCES±0.05MM

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司			
▽⁰ ▽^C⁰		MM		INCH	MATERIAL:	HRC:	TITLE: Battery 2.0PH 180度DIP 公座 系列图				
	. X	±0.25	. X	Ⓢ	DRAWN BY DATE JK-YANG						
	. XX	±0.15	. XX	Ⓢ	CHECKED BY DATE						
	. XXX	±0.05	. XXX	Ⓢ	APPROVED BY DATE						
	ANGULAR ±1°				PART NO. JME20Mxx-H575001A-B		THIRD ANGLE PROJECTION		REVISE ON CAD ONLY		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							DWG NO. JMEA05-A180PC2603		SHEET NO. 1/1		