





	1	2	3	4	5	6	7	8
RoHS							13.85	15.0
REACH							11.85	$\varnothing 3.0$
							8.35	$\varnothing 3.2$
A							7.85	$\varnothing 3.3$
B							6.85	$\varnothing 3.3$
C							6.35	$\varnothing 3.3$
D							5.35	$\varnothing 3.3$
E							4.85	$\varnothing 3.3$
F							3.85	$\varnothing 3.5$
G							3.15	$\varnothing 3.5$
H							高度L(mm)	帽头H(mm)
								直径A(mm)

①—○—○—②

③—○—④— \bar{z}

电路图

未注尺寸公差(mm)				设计				产品名称:轻触开关					
0~3	± 0.05	± 0.10	± 0.20										
$>3~6$	± 0.05	± 0.10	± 0.30	审核				产品型号:TC-06D-01-5H					
$>6~30$	± 0.10	± 0.20	± 0.50									产品规格:	
$>30~120$	± 0.15	± 0.30	± 0.80					标准化					
角度	$\pm 1^\circ$											批准	