

RoHS
Compliant

SYMBOL

SPECIFICATIONS

1. ELECTRICAL CHARACTERISTICS:

1-1. RATING: DC 12V 15A / Pin

1-2. CONTACT RESISTANCE: 30mΩ

1-3. DIELECTRIC WITHSTANDING VOLTAGE:

500V AC FOR ONE MINUTE

1-4. INSULATION RESISTANCE: 500MΩ ,
MEASURED BY 500V DC

2. LIFE TEST: MECHANICAL LIFE TEST 5,000 CYCLES.

3. TEMPERATURE RISE : 30° C MAX


规格型号	DIM:A	DIM:B	DIM:C
JME-DC30F-A-2P-R1-B	9.50	7.50	3.00
JME-DC30F-A-3P-R1-B	12.50	10.50	6.00
JME-DC30F-A-4P-R1-B	15.50	13.50	9.00
JME-DC30F-A-5P-R1-B	18.50	16.50	12.00
JME-DC30F-A-6P-R1-B	21.50	19.50	15.00
JME-DC30F-A-7P-R1-B	24.50	22.50	18.00
JME-DC30F-A-8P-R1-B	27.50	25.50	21.00
JME-DC30F-A-9P-R1-B	30.50	28.50	24.00
JME-DC30F-A-10P-R1-B	33.50	31.50	27.00
JME-DC30F-A-11P-R1-B	36.50	34.50	30.00
JME-DC30F-A-12P-R1-B	39.50	37.50	33.00

2	HOUSING	PA9T	1	BLACK
1	CONTACT TERMINAL	C70250	7	Au PLATED
NO.	PARTS	MATERIAL	QTY.	FINISHING



深圳市文章济美科技有限公司

COPYRIGHT RESERVED, PLEASE DO NOT COPY.

PART NAME		CONNECTOR		DRAWING	Y. C. Zhang	DWG. No.	
PART NO.		JME-DC30F-A-xxP-R1-B		CHECK	G. C. Chen	REV.	A1
	UNIT :	TOLERANCE	X. ±0.15 X.* ±1°	ANGLE	APPROVAL	DATE	12-12-2022
	mm	OTHERWISE	X.X ±0.10 X.X* ±0.5° X.XX ±0.05 X.XX ±0.05° X.XXX ±0.005 X.XXX ±0.005°	0° ±3°	SCALE	PAGE	1 OF 1



3D VIEW



PCB LAYOUT

