

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK		120606

Material

Insulator:Nylon 9T(UL94V-0)

Contact:phosphor Bronze

Contact Plated:Gold over Nickel or Tin

Specification

Current rating:5A

instant CURRENT:7A



Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°

No:of pins	Dimension			
	DIM.A	DIM.B	DIM.C	DIM.D
02	2.50	6.50	9.45	2.50
03	5.00	9.00	11.95	5.00
04	7.50	11.50	14.45	7.50
05	10.00	14.00	16.95	10.00
06	12.50	16.50	19.45	12.50
07	15.00	19.00	21.96	15.00
08	17.50	21.50	24.45	17.50
09	20.00	24.00	26.95	20.00
10	22.50	26.50	29.45	22.50
11	25.00	29.00	31.95	25.00
12	27.50	31.50	34.45	27.50
13	30.00	34.00	36.95	30.00
14	32.50	36.50	39.45	32.50
15	35.00	39.00	41.95	35.00
16	37.50	41.50	44.45	37.50



Recommended P.C.B Layout

Layout Tolerance=+/-0.05mm

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司	
		MM		INCH	MATERIAL:	HRC:		
▽ r0	. X	±0.25	. X	②	DRAWN BY	DATE	TITLE: Battery 2.5PH 90度SMT 有柱	
	. XX	±0.15	. XX	③	CHECKED BY	DATE		
	. XXX	±0.05	. XXX	④	APPROVED BY	DATE	THIRD ANGLE PROJECTION	
▽ C r0	ANGULAR ±1°				PART NO.		REVISE ON CAD ONLY	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DWG NO.		SHEET NO. 1/1	
							A4	