

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK	Yang	120606

Material

Insulator:Nylon 9T(UL94V-0)

Contact:phosphor Bronze

Contact Plated:Gold over Nickel or Tin

Specification

Current rating:5A





instant CURRENT:7A

Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°



PARTNUMBER	No:of pins	Dimension			
		DIM.A	DIM.B	DIM.C	DIM.D
JME25Fxx-H650001A-B	02	2.50	6.50	9.45	2.1/3.0
JME25Fxx-H650001A-B	03	5.00	9.00	11.95	2.1/3.0
JME25Fxx-H650001A-B	04	7.50	11.50	14.45	2.1/3.0
JME25Fxx-H650001A-B	05	10.00	14.00	16.95	2.1/3.0
JME25Fxx-H650001A-B	06	12.50	16.50	19.45	2.1/3.0
JME25Fxx-H650001A-B	07	15.00	19.00	21.95	2.1/3.0
JME25Fxx-H650001A-B	08	17.50	21.50	24.45	2.1/3.0
JME25Fxx-H650001A-B	09	20.00	24.00	26.95	2.1/3.0
JME25Fxx-H650001A-B	10	22.50	26.50	29.45	2.1/3.0
JME25Fxx-H650001A-B	11	25.00	29.00	31.95	2.1/3.0
JME25Fxx-H650001A-B	12	27.50	31.50	34.45	2.1/3.0
JME25Fxx-H650001A-B	13	30.00	34.00	36.95	2.1/3.0
JME25Fxx-H650001A-B	14	32.50	36.50	39.45	2.1/3.0
JME25Fxx-H650001A-B	15	35.00	39.00	41.95	2.1/3.0
JME25Fxx-H650001A-B	16	37.50	41.50	44.45	2.1/3.0

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司			
▽⁰ ▽^C/₀			MM		INCH	MATERIAL:		HRC:					
		. X ±0.25		. X		ⓐ		DRAWN BY _____ DATE _____ JK-YANG		TITLE: Battery 2.5PH 180度DIP无柱 母座			
		. XX ±0.15		. XX		ⓑ							
		. XXX ±0.05		. XXX		ⓒ		CHECKED BY _____ DATE _____		ⓐⓑⓒ THIRD ANGLE PROJECTION		REVISE ON CAD ONLY	
		ANGULAR ±1°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						APPROVED BY _____ DATE _____		PART NO. JME25Fxx-H650001A-B		DWG NO.		SHEET NO. 1/1	