

NOTES:

额定电流 Current rating: 0.5A

额定电压 Voltage rating: 50V

耐电压 Withstand voltage: 500V AC/minute

接触电阻 Contact resistance : $\leq 40\text{m}\Omega$ 绝缘电阻 Insulation resistance: $100\text{M}\Omega$ MIN工作温度 Working temperature: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

盐雾测试 Salt spray test: 24H

触点高低PIN不大于0.05mm.

Part No	Pin	A	B	C	D	E	F
XY-FPC-05F-10-4RLTAG	4	6.4	1.50	2.55	2.50	1.50	1.50
XY-FPC-05F-10-6RLTAG	6	7.4	2.50	3.55	3.50	2.50	2.50
XY-FPC-05F-10-8RLTAG	8	8.4	3.50	4.55	4.50	3.50	3.50
XY-FPC-05F-10-10RLTAG	10	9.4	4.50	5.55	5.50	4.50	4.50
XY-FPC-05F-10-12RLTAG	12	10.4	5.50	6.55	6.50	5.50	5.50
XY-FPC-05F-10-14RLTAG	14	11.4	6.50	7.55	7.50	6.50	6.50
XY-FPC-05F-10-16RLTAG	16	12.4	7.50	8.55	8.50	7.50	7.50
XY-FPC-05F-10-18RLTAG	18	13.4	8.50	9.55	9.50	8.50	8.50
XY-FPC-05F-10-20RLTAG	20	14.4	9.50	10.55	10.50	9.50	9.50
XY-FPC-05F-10-22RLTAG	22	15.4	10.50	11.55	11.50	10.50	10.50
XY-FPC-05F-10-24RLTAG	24	16.4	11.50	12.55	12.50	11.50	11.50
XY-FPC-05F-10-26RLTAG	26	17.4	12.50	13.55	13.50	12.50	12.50
XY-FPC-05F-10-28RLTAG	28	18.4	13.50	14.55	14.50	13.50	13.50
XY-FPC-05F-10-30RLTAG	30	19.4	14.50	15.55	15.50	14.50	14.50
XY-FPC-05F-10-32RLTAG	32	20.4	15.50	16.55	16.5	15.50	15.50
XY-FPC-05F-10-34RLTAG	34	21.4	16.5	17.55	17.5	16.5	16.5
XY-FPC-05F-10-36RLTAG	36	22.4	17.5	18.55	18.5	17.5	17.5
XY-FPC-05F-10-40RLTAG	40	24.4	18.5	20.55	20.5	18.5	18.5
XY-FPC-05F-10-50RLTAG	50	29.4	24.5	25.55	25.5	24.5	24.5

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR. Alex	TITLE: FPC 0.5PH H2.0 前下接		
.XX±0.25	.X.*± 3°	CHK. Jack	DWG NO. XY-FPC-05F-10-NRLTAG		
.XXX±0.15	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1