



RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	新版发型		JACK	Yang	190918



P.C.B LAYOUT
TOLERANCE: ±0.05

备注:

1. 材料: LCP黑色, 黄铜镀金;
1. 额定电压: AC/DC 30V Max
2. 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
3. 绝缘电阻: DC 500V 1 MINUTE, 1000MΩ Min
4. 操作温度: -20° to +80°

Table:

PART NUMBER	P / N	Dim. A	Dim. B	Dim. C
JME2Mxx-H725001AZ-B	03pin	6.50	5.90	4.00
JME2Mxx-H725001AZ-B	04pin	8.50	7.90	6.00
JME2Mxx-H725001AZ-B	05pin	10.50	9.90	8.00
JME2Mxx-H725001AZ-B	06pin	12.50	11.90	10.00
JME2Mxx-H725001AZ-B	07pin	14.50	13.90	12.00
JME2Mxx-H725001AZ-B	08pin	16.50	15.90	14.00

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		SHEET: 1/1		东莞市文章济美电子有限公司			
▽-0		MM			INCH		REVISION:		TITLE:				
	-X	±0.25		-X	②----		DRAWN BY JK-YANG		DATE		Battery 2.0 PH H=7.25mm公座		
	-XX	±0.15		-XX	③----		CHECKED BY		DATE		 THIRD ANGLE PROJECTION		
	-XXX	±0.05		-XXX	④----		APPROVED BY		DATE				
C-0	ANGULAR ±1°						DESIGNED BY		DATE		REVIEW BY CAD CHECK		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						REVISION NO.		DATE		1/1		
							JME2Mxx-H725001AZ-B				A4		