

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK	Yang	1503015

NOTE:

Material

Insulator:Nylon 9T(UL94V-0)

Contact:phosphor Bronze

Contact Plated:Gold over Nickel
or Tin

Specification

Current rating:7A





instant CURRENT:10A

Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°



P. C. B LAYOUT
TOLERANCE: ±0.05

PARTNUMBER	No:of pins	Dimension			
		DIM.A	DIM.B	DIM.C	DIM.D
JME20Mxx-H490001BC-B	03	11.65	4.00	9.15	10.25
JME20Mxx-H490001BC-B	04	13.65	6.00	11.15	12.25
JME20Mxx-H490001BC-B	05	15.65	8.00	13.15	14.25
JME20Mxx-H490001BC-B	06	17.65	10.00	15.15	16.25
JME20Mxx-H490001BC-B	07	19.65	12.00	17.15	18.25
JME20Mxx-H490001BC-B	08	21.65	14.00	19.15	20.25
JME20Mxx-H490001BC-B	09	23.65	16.00	21.15	22.25
JME20Mxx-H490001BC-B	10	25.65	18.00	23.15	24.25
JME20Mxx-H490001BC-B	11	27.65	20.00	25.15	26.25
JME20Mxx-H490001BC-B	12	29.65	22.00	27.15	28.25
JME20Mxx-H490001BC-B	13	31.65	24.00	29.15	30.25
JME20Mxx-H490001BC-B	14	33.65	26.00	31.15	32.25
JME20Mxx-H490001BC-B	15	36.65	28.00	33.15	34.25

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司		
▽⁰ ▽^C⁰		MM		INCH	MATERIAL:	IBC:	TITLE: Batory 2.0PH 90度DIP带鱼叉 公座/平针			
	. X	±0.25	. X	②	DRAWN BY DATE JK-YANG					
	. XX	±0.15	. XX	③	CHECKED BY DATE		③④ THIRD ANGLE PROJECTION	REVISE ON CAD ONLY		
	. XXX	±0.05	. XXX	④	APPROVED BY DATE					PART NO. JWE20Mxx-H490001BC-B
	ANGULAR ±1°									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										