




RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000MΩ, Min
Contact Resistance: 20mΩ, Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
XY-IDC2.0-2*3P	2*3	4.00	6.00
XY-IDC2.0-2*4P	2*4	6.00	8.00
XY-IDC2.0-2*5P	2*5	8.00	10.00
XY-IDC2.0-2*6P	2*6	10.00	12.00
XY-IDC2.0-2*7P	2*7	12.00	14.00
XY-IDC2.0-2*8P	2*8	14.00	16.00
XY-IDC2.0-2*9P	2*9	16.00	18.00
XY-IDC2.0-2*10P	2*10	18.00	20.00
XY-IDC2.0-2*11P	2*11	20.00	22.00
.....			
XY-IDC2.0-2*35P	2*35	PIN-2.00	PIN

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.35	X.*± 5°	APR.	Alex	TITLE: 2.0DC3-nPin H5.7 180# PC2.8 L8.0 6T			
.XX±0.2	.X*± 1	CHK.	Jack	DWG NO. XY-IDC2.0-2*NP			
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A