

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK	Yang	150801

A

B

C

D

E

F

A

B

C

D

E

F






Table:

PART NUMBER	P / N	Dim. A	Dim. B	Dim. C
JME2F02-H250001T-B	02pin	6.00	2.00	5.35
JME2F03-H250001T-B	03pin	8.00	4.00	7.35
JME2F04-H250001T-B	04pin	10.00	6.00	9.35
JME2F05-H250001T-B	05pin	12.00	8.00	11.35
JME2F06-H250001T-B	06pin	14.00	10.00	13.35
JME2F07-H250001T-B	07pin	16.00	12.00	15.35
JME2F08-H250001T-B	08pin	18.00	14.00	17.35

备注:

- 1.额定电流: 3.0A > PIN
- 2.额定电压: 30V(Max) AC/DC;
- 3.绝缘耐压: AC 1KV 1分钟相邻端子间无损坏
- 4.绝缘阻抗: 1000M Ω , 500V DC/1分钟相邻端子间无损坏
- 5.使用温度: -40 ~ +85 $^{\circ}$ C
- 6.主体材质: LCP/PBT/耐温260 $^{\circ}$ $\pm$ 5 $^{\circ}$
- 7.五金材质: 磷铜镀金 (T=0.20mm)

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司	
	MM	INCH			MATERIAL:	HRC:		
∇ 0	.X $\pm$ 0.25	.X $\pm$			DRAWN BY JK-YANG	DATE	TITLE: MINI 2.0PH 2.5H SMT 母座	
∇ C 0	.XX $\pm$ 0.15	.XX $\pm$			CHECKED BY	DATE		
	.XXX $\pm$ 0.05	.XXX $\pm$			THIRD ANGLE PROJECTION		REVISE ON CAD ONLY	
	ANGULAR $\pm$ 1 $^{\circ}$				APPROVED BY	DATE	PART NO.	DWG. NO. JME2Fxx-H250001T-B
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							SHEET NO. 1/1

A4