

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK		150306

Material

Insulator:Nylon 9T(UL94V-0)

Contact:phosphor Bronze

Contact Plated:Gold over Nickel or Tin

Specification

Current rating:5A





instant CURRENT:7A

Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°



Recommended P.C.B Layout
Layout Tolerance=+/-0.05mm

PARTNUMBER	No:of pins	Dimension				
		DIM.A	DIM.B	DIM.C	DIM.D	DIM.E
JME25Fxx-H650001AZ-B	02	2.50	6.50	9.45	5.50	2.1/3.0
JME25Fxx-H650001AZ-B	03	5.00	9.00	11.95	8.00	2.1/3.0
JME25Fxx-H650001AZ-B	04	7.50	11.50	14.45	10.50	2.1/3.0
JME25Fxx-H650001AZ-B	05	10.00	14.00	16.95	13.00	2.1/3.0
JME25Fxx-H650001AZ-B	06	12.50	16.50	19.45	15.50	2.1/3.0
JME25Fxx-H650001AZ-B	07	15.00	19.00	21.95	18.00	2.1/3.0
JME25Fxx-H650001AZ-B	08	17.50	21.50	24.45	20.50	2.1/3.0
JME25Fxx-H650001AZ-B	09	20.00	24.00	26.95	23.00	2.1/3.0
JME25Fxx-H650001AZ-B	10	22.50	26.50	29.45	25.50	2.1/3.0
JME25Fxx-H650001AZ-B	11	25.00	29.00	31.95	28.00	2.1/3.0
JME25Fxx-H650001AZ-B	12	27.50	31.50	34.45	30.50	2.1/3.0
JME25Fxx-H650001AZ-B	13	30.00	34.00	36.95	33.00	2.1/3.0
JME25Fxx-H650001AZ-B	14	32.50	36.50	39.45	35.00	2.1/3.0
JME25Fxx-H650001AZ-B	15	35.00	39.00	41.95	37.50	2.1/3.0
JME25Fxx-H650001AZ-B	16	37.50	41.50	44.45	39.50	2.1/3.0

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司	
	MM	INCH	⑩	⑪	MATERIAL:	HRC:		
▽ ⁰	. X ±0.25	. X	⑩	⑪	DRAWN BY	DATE	TITLE: Battery 2.5PH 180度中柱 母座	
▽ ^C	. XX ±0.15	. XX	⑩	⑪	CHECKED BY	DATE		
	. XXX ±0.05	. XXX	⑩	⑪	APPROVED BY	DATE	THIRD ANGLE PROJECTION	
	ANGULAR ±1°				PART NO. JME25Fxx-H650001AZ-B		REVISE ON CAD ONLY	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DWG. NO.		SHEET NO. 1/1	