

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK		150606

Material

Insulator:Nylon 9T(UL94V-0)

TERMINAL:phosphor Bronze

TERMINAL Plated:Gold over Nickel
or Tin

Specification

Current rating:7A

instant CURRENT:10A



Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V

Operdting Temperature:-40°~105°

No. of Pins	Dimension	
	DIM. A	DIM. B
02	7.00	2.50
03	9.50	5.00
04	12.00	7.50
05	14.50	10.00
06	17.00	12.50
07	19.50	15.00
08	22.00	17.50
09	24.50	20.00
10	27.00	22.50
11	29.50	25.00
12	32.00	27.50
13	34.50	30.00
14	37.00	32.50
15	39.50	35.00
16	42.00	37.50



Recommended P.C.B Layout
Layout Tolerance=+/-0.05mm

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司									
▽_A		MM		INCH	MATERIAL:	HRC:		TITLE: Battery PH2.5mm 180度DIP 5.8H 公座									
	.X	±0.25	.X	②	DRAWN BY		DATE										
	.XX	±0.15	.XX	③	CHECKED BY		DATE		⌀ THIRD ANGLE PROJECTION		REVISE ON CAD ONLY						
	.XXX	±0.05	.XXX	④													
	ANGULAR ±1°				APPROVED BY		DATE						PART NO. JME2510xx-H058001A-B		DWG NO.		SHEET NO. 1/1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																	
▽_C																	