

	1	2		3				4	5	6	7	8				
A	linear dimension(Tolerances Standard GB/T 14486-2008)								—	□	⊥	版本 Version	描述 Description	设计 Design	批准 Approved	日期 Date
	variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	to 10	over 10 to 100	over 100 to	A	新发行	熊武敌	楼特高	2024.03.10	
	tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60					
B																
C																
D																
E	编码原则(Product Number Code): WJ2EDGKBM-5.08-XXP-1Y-00A 产品型号(Series No.) 间距(Pitch) 极数(No. of Poles) 客户需求(Customer Request) 塑体颜色(Housing Color) 1:单倍间距(Single Pitch) 2:双倍间距(Double Pitch) 1:灰色(Grey) 6:红色(Red) 2:蓝色(Blue) 7:透明(Transparent) 3:黑色(Black) 8:黄色(Yellow) 4:绿色(Green) 9:白色(White) 5:橙色(Orange)															
F																
G																
H																

材质及电镀 MATERIAL	
螺丝 Screws	M2.5, 钢, 镀锌 M2.5, Steel, Zn plated
夹片 Clamp	铜合金, 镀镍 Copper alloy, Ni plated
方块 Cage	铜合金, 镀镍 Copper alloy, Ni plated
塑件 Housing	PA66, UL94V-0
电气性能 ELECTRICAL	
参考标准 Stanard	UL IEC
额定电压 Rated voltage	300V 320V
额定电流 Rated current	10A 15A
使用线径 Wire range	24-12AWG 2.5mm²
接触电阻 Contact resistance	20mΩ
绝缘电阻 Insulation resistance	500MΩ/DC500V
耐电压 Withstanding voltage	AC1600V/1Min
机械性能 MECHANICAL	
温度范围 Temp.range	-40℃~+105℃
瞬时温度 Max.soldering	+250℃ for 5 Sec
扭矩 Torque	4.08kgf.cm/0.4N.m
剥线长度 Strip length	7~8mm

第三视角 (THIRD ANGLE PROJECTION)				插拔式接线端子 PLUG-IN TERMINAL BLOCK			
图纸类型 (TYPE)		CUSTOMER DRAWING		型号 (NAME)		WJ2EDGKBM-5.08-XXP-1Y-00A	
单位 (UNITS)		mm		版本 (VERSION)		A	
尺寸 (SIZE)		A4		比例 (SCALE)		1:1	
图页 (SHEET)		1/1		KANGNEX NBWJ		宁波康奈克斯电气有限公司 NINGBO KANGNEX ELECTRIC., LTD.	