



SPECIFICATION:

Current Rating:2.0AMP

Contact Resistance:20m Ω (max)

Insulation Resistance:1000M Ω Min at 500V DC

Dielectric Strength:500V AC Per 1 Minute

Operating Temperature:-40℃ TO +105℃

MATERIALS:

Insulator:Nylon 6T Glass Fibre(UL 94V-0)

Contact:Brass

Contact plated: Gold Over Nickel

CONTACTS	PART NO.	A	B	C
8	B-3102S08P-A000	8.0	23.9	6.0
10	B-3102S10P-A000	10.0	25.9	8.0
12	B-3102S12P-A000	12.0	27.9	10.0
14	B-3102S14P-A000	14.0	29.9	12.0
16	B-3102S16P-A000	16.0	31.9	14.0
20	B-3102S20P-A000	20.0	35.9	18.0
22	B-3102S22P-A000	22.0	37.9	20.0
24	B-3102S24P-A000	24.0	39.9	22.0
26	B-3102S26P-A000	26.0	41.9	24.0
30	B-3102S30P-A000	30.0	45.9	28.0
32	B-3102S32P-A000	32.0	47.9	30.0
34	B-3102S34P-A000	34.0	49.9	32.0
40	B-3102S40P-A000	40.0	55.9	38.0
44	B-3102S44P-A000	44.0	59.9	42.0
50	B-3102S50P-A000	50.0	65.9	48.0

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 310-2S-XP 长耳			
DRAWN: YAN	DATE: 2011-12-12	CLIENT P/N	B-3102SXXP-A000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-310-00010		REV. A