









RECOMMENDED PCB PATTERN LAYOUT



NOTES:

1.ELECTRICAL PERFORMANCE:
CURRENT RATING:0.5A AT AC 100V.
WITHSTAND VOLTAGE:250V AC.
CONTACT RESISTANCE:BEFORE TEST: ≤ 40mΩ
AFTER TEST: ≤ 60mΩ
INSULATLON RESISTANCE:1000MΩ Min.
OPERATION TEMPERATURE:-55°C TO +105°C

2:MATERIAL
HOUSING:LCP BLACK UL94V-0
TERMINAL:COPPER ALLOY T=0.20
CAP:SUS T=0.20

3:ELECTROPLATING:
OVERALL NICKEL PLATING 50U TERMINAL,
GILT CONTACT AREA 10U.
TIN PLATING 100U SMT AREA.

MATED HEIGHT		
PLUG	SOCKET H2	
H1	8.00	10.00
5.00	10.00	12.00
6.00	11.00	13.00

NO	67.77	66.17	62.865	71.37	200
	61.42	59.82	56.515	65.02	180
	55.07	53.47	50.165	58.67	160
	48.72	47.12	43.815	52.32	140
	42.37	40.77	37.465	45.97	120
	36.02	34.42	31.115	39.62	100
	32.85	31.25	27.94	36.45	90
YES	29.67	28.07	24.765	33.27	80
	26.5	24.9	21.59	30.1	70
	23.32	21.72	18.415	26.92	60
	20.15	18.55	15.24	23.75	50
	16.97	15.37	12.065	20.57	40
	13.8	12.2	8.89	17.4	30
	10.62	9.02	5.715	14.22	20

HS'G LOCK	D	C	B	A	CKT. NO.
-----------	---	---	---	---	----------

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD

制图 (DR):	Jerry 2022.09.09	品名(TITLE):	0.635 PITCH BTOB SOCKET
审核 (CHKD):		料号(PART NO):	LB17**-*S-WOR
核准 (APPD):	Tong 2022.09.09	比例(SCALE):	1:1
		单位(UNITS):	mm
		张数(SHEET):	1 OF 1
		图幅(SIZE):	A4

RoHS
Compliant
2013/95/EC



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差 GENERAL TOLERANCE
.X ±0.35
.XX ±0.25
.XXX ±0.05
ANGLES ±1°

