






3D VIEW



RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)

RECOMMENDED MATAL MASK T=0.12mm

SMT SOLDER AREA

NO PATTERN AND VIA HOLE IN HTIS AREA

NOTES:

1.MATERIAL:

HOUSING: High Temperature Thermoplastic
Terminal:Copper Alloy
Shell: Stainless Steel


2.PLATING:

Terminal:30u" Ni UNDERPLATED OVERALL
G/F PLATED ON CONTACT AREA AND SOLDER AREA
Sheel:30u" Ni UNDERPLATED OVERALL
G/F PLATED ON CONTACT AREA AND SOLDER AREA

3.TECHNICAL SPECIALITY:


RATED VOLTAGE: 30V AC MAX.
CURRENT RATING: 0.5A MAX.
INSULATION RESISTANCE:1000MΩ MIN
CONTACT REISTANCE:100mΩ MAX
WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTES
OPERATING TEMPERATURE: -40°C~+85°C
Humidity 80% R.H MAX

4.DIMENSIONS WITH MARK" * "MUST BE MEASURE BY QC AND IPQC




PIIN/NO	ASSIGNMENT	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
C1	VCC			PART NO. NANO-113-7P	TITLE: 1.37H NANO SIM CARD CONNECTOR(L型) 无#	DESIGN: Ethan	MANUFACTURE DWG
C2	RST	.X±0.30	X.*±3°				
C3	CLK	.XX±0.20	X.X*±2°	CHED: Olvia	APPD: Ava	SCALE N:A	SHEET 1/2
CD	Detect Switch	.XXX±0.10					
C5	GND	UNITS	mm	FINISH	---	---	---
C6	VPP	MATERILA	---				
C7	I/O						

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




NOTES

1. NUMBER OF CONNECTORS: 1500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 15000PCS/CARTON
4. WEIGHT :
 - 3.1 NET WEIGHT : Kg
 - 3.2 GROSS WEIGHT : Kg



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.*±3°	PART NO. NANO-113-7P	TITLE: 1.37H NANO SIM CARD CONNECTOR(L型) 无#	
.XX±0.20	X.X°±2°			
.XXX±0.10				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	---	CHED: Olvia		
FINISH	---	APPD: Ava		
			SCALE N:A	SHEET 2/2