




HAOYU



P.C.B LAYOUT

MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	Ø1.45	Ø2.0	Ø2.35	Ø2.5
APPD.				

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		UP TO 5mm: ±0.1	ANGULAR ±1°	A1	2017.04.28	更新材质		GYW		
						NO	DATE			REVISIONS		BY	APPD			
6	DC005 PING	BRASS	1	Ni PLATED												
5	DC005 4#FLAT PIECE 2.5	BRASS	1	Ag PLATED				ABOVE 5mm: ±0.2								
4	DC005 2#CURVE PIECE 2.5	BRASS	1	Ag PLATED												
3	DC005 3#SPRING 2.5	PBS/SUS	1	Ag PLATED												
2	DC005 COVER	PBT	1	BLACK/RED/YELLOW												
1	DC005 CASE	PBT	1	BLACK/RED/YELLOW												
NO.		PART	NAME	MATERIAL	QTY	FINISHING										



HAOYU(HONGKONG)LIMITED
皓宇(香港)有限公司

PRO.AGL:

REV :A1