






备注:

电气性能:

接触阻抗: 30毫欧(最大)

绝缘阻抗: 1000兆欧(最小)


耐高压: 500V AC一分钟

电镀:

端子: 接触区域镀金

焊接区镀亮锡 100u"Min

外壳: 全区域镀镍 50u"Min



PCB.LAYOUT

TOL: ±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±2°	PART NO. USB-WJDG-AF90	TITLE: USB AF 90度 弯脚有盖		
.XX±0.20	X.X°±1°				
.XXX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1