






<i>PIN</i>	$\phi 2.0$	$\phi 2.5$
<i>APPD.</i>		

力度要求：插力11N-20N，拔力12-20N。
(常规不带凹槽插头)

					TOLERANCE UNLESS SPECIFIED								
							A1	2023.05.26	新增黑色, 绿色规格			GYW	
6	DC005 PING	BRASS	1	Ni PLATED	UP TO 5mm:±0.1	ANGULAR ±1°	A0	2016.12.22	新版发行			GYW	
5	DC005 4#FLAT PIECE	BRASS	1	Ag PLATED	ABOVE 5mm:±0.2		NO	DATE	REVISIONS			BY	APPD
4	DC005 2#CURVE PIECE	BRASS	1	Ag PLATED	TITLE:DC JACK				UNIT : MM	ROHS COMPLIANT	DWN		
3	DC005Q 3#SPRING	SUS	1	Ag PLATED	MODEL: DC-005QB ϕ 2.0-SU-L				SCALE: 5:1		CHK'D		
2	DC005 COVER	PBT	1	RED/BLACK/GREEN	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD			
1	DC005Q CASE	PBT	1	RED/BLACK/GREEN						PRO.AGL: 	REV: A1		
NO.	PART NAME	MATERIAL	QTY	FINISHING									