



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

说明:

1.材质:

胶芯:LCP,UL94V-0; COLOR; BLACK

端子:C2680

外壳:SPCC/C2680

2.电镀说明:

端子:接触区域镀金

焊锡区域镀锡100 u"Min

全部区域镀底50 u" Min

外壳:表面镀镍100 u" Min

3.电气性能:








绝缘阻抗 (EIA-364-21):100 MΩ MIN.

AT 500V/DC FOR 1 MINUTE.

接触阻抗 (EIA-364-06) 30 mΩ MAX.

耐电压 (EIA-364-20) NO DISCHARGE,
FLASHOVER OR BREAKDOWN
AT 500 V/AC 1MINUTE.

4.工作温度:-40℃ to +85℃



RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

1	TMDS Data2+	11	TMDS Clock Shield
2	TMDS Data2 Shield	12	TMDS Clock-
3	TMDS Data2-	13	CEC
4	TMDS Data 1+	14	Reserved (N.C)
5	TMDS Data 1 Shied	15	SCL
6	TMDS Data 1-	16	SDA
7	TMDS Data 0+	17	DDC/CEC Ground
8	TMDS Data 0 Shield	18	+5V Power
9	TMDS Data 0-	19	Hot Plug Detect
10	TMDS Clock+		

TOLERANCE



深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

.X±0.30	.X'±3"	PART NO. HDMI-019S	TITLE: HDMI A TYPE 板上型		
.XX±0.20	.XX'±2"		MANUFACTURE DWG		
.XXX±0.10					
UNITS	mm	DESIGN: Ethan	 SCALE N:A		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			