




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- MATERIAL:

 - Insulator:PBT+30%Glass Fiber
 - Contact:Brass
 - Contact Plated: Au 1u" Plated
 - Shell:Steel,Nickel Plated
- SPECIFICATION:

 - Current Rating:3 AMPS
 - Insulation Resistance: 100MΩ MIN. At 500VDC
 - Dielectric Strength: 500V for One minute
 - Operation Temperature: -55° C~+105° C.
- * 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO.	TITLE:		
.XX±0.25	X.X*±2°	D-SUB-DMR9PF-D002	DR9F叉锁		
.XXX±0.15	X.XX*±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1