




备注:

1) 材质:

1-1 本体:LCP 94V-0 黑色

1-2 端子:C2680 T=0.15mm

1-3 铜壳:C2680 T=0.50mm

2) 镀层:

2-1 端子:所有面镀镍,接点镀金,

焊脚镀锡 50u"MIN,盐雾测试48H无氧化生锈,锡区除外

3) 技术规格

3-1.额定电压:40V

3-2.额定电流:0.5A

3-3.绝缘电阻:100兆欧最小


3-4.接触电阻:30毫欧最大

3-5.操作温度:-20度到85度


3-6.插入力:44.1N Max

3-7.拔出力:9.8~39.2N;

3-8.耐久:10000次



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05



3	CONTACT	19	C2680R-H	PLATED Au
2	SHELL	1	C2680R-H	PLATED Ni
1	HOUSING	1	LCP	UL94V-0,Black
NO.	ITEM	Q'TY	DESCRIPTION	FINISH
TOLERANCE			深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
.X±0.25	X.*±1.5°	PART NO. HDMI-01-19P	TITLE: HDMI 19P A/F 2.1VER	MANUFACTURE DWG
.XX±0.15	X.X*±1.0°			
.XXX±0.10	X.XX*±0.5°			
UNITS	mm	DESIGN:	Ethan	
MATERILA	— — —	CHED:	Olvia	
FINISH	— — —	APPD:	Ava	
				SCALE N:A
				SHEET 1/2

