



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



NOTES:
1.HUOSING:LCP HGH-TEMP
THERMOPLASTIC UL94V-0
2.TERMINAL:PHOSPHOR BRONZE
3.COLOR:BEIGE



SOCKET H1	MATED HEIGHT				
	PLUG H				
	4.70	5.70	6.70	7.70	
3.70	5.00	6.00	7.00	8.00	
7.70	9.00	10.00	11.00	12.00	
11.70	13.00	14.00	15.00	16.00	
15.70	17.00	18.00	19.00	20.00	

Model	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
JXT-40DS-0850C	40	21.80	15.20	16.80	20.20	18.80	20.15
JXT-50DS-0850C	50	25.80	19.20	20.80	24.20	22.80	24.15
JXT-60DS-0850C	60	29.80	23.20	24.80	28.20	26.80	28.15
JXT-80DS-0850C	80	37.80	31.20	32.80	36.20	34.80	36.15
JXT-100DS-0850C	100	45.80	39.20	40.80	44.20	42.80	44.15
JXT-120DS-0850C	120	53.80	47.20	48.80	52.20	50.80	52.15
JXT-140DS-0850C	140	61.80	55.20	56.80	60.20	58.80	60.15
JXT-160DS-0850C	160	69.80	63.20	64.80	68.20	66.80	68.15
JXT-180DS-0850C	180	77.80	71.20	72.80	76.20	74.80	76.15
JXT-200DS-0850C	200	85.80	79.20	80.80	84.20	82.80	84.15

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.25	±1°	PART NO.	TITLE: 0.8mm PITCH BTB CONNECTOR SOCKET	
.XX±0.20		JXT-NDS-0850C		
.XXX±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		
MATERILA	— — —	APPD: Ava		
FINISH	— — —		SCALE	SHEET
			N:A	1/1