




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




-, MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

-, SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55 $^{\circ}$ C ~ +105 $^{\circ}$ C.

* 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ± 0.05

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X ± 0.30	X.* $\pm 5^{\circ}$	PART NO.	TITLE: DR9M双锁		
.XX ± 0.25	X.X* $\pm 2^{\circ}$	D-SUB-DMR9PM-D002			
.XXX ± 0.15	X.XX* $\pm 1^{\circ}$	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava		SCALE	SHEET
FINISH	— — —			N:A	1/1