




SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/0.3A AC;
- 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN;
- 4.CONTACT RESISTANCE: 100m Ω MAX;
- 5.OPERATING TEMPERATURE RANGE: -35°C TO 85°C.

MATERIAL:

- 1.INSULATOR: LCP UL 94V-0 BLACK;
- 2.TERMINAL: COPPER ALLOY;
- 3.METAL FITTINGS: COPPER ALLOY.

PLATING:

- 1.TERMINAL: GOLD PLATING, NICKEL 50u" MIN. OVER ALL;
- 2.METAL FITTINGS: TIN 100u" MIN. OVER NICKEL 50u"MIN.

Model	PIN	DIM A	DIM B	DIM C
JXT-10DS-0408	10	4.50	3.40	1.60
JXT-12DS-0408	12	4.90	3.80	2.00
JXT-16DS-0408	16	5.70	4.60	2.80
JXT-20DS-0408	20	6.50	5.40	3.60
JXT-24DS-0408	24	7.30	6.20	4.40
JXT-30DS-0408	30	8.50	7.40	5.60
JXT-34DS-0408	34	9.30	8.20	6.40
JXT-40DS-0408	40	10.50	9.40	7.60
JXT-50DS-0408	50	12.50	11.40	9.60

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.25	±1°	PART NO. JXT-NDs-0408	TITLE: BTB P0.40 SOCKET		
.XX±0.20					
.XXX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olvia		SCALE N:A	SHEET 1/1
FINISH	— — —	APPD: Ava			