

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN





− MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated

− SPECIFICATION:

- 1.Current Rating:5 AMPS
- 2.Insulation Resistance: 100M Ω MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: −55° C~+105° C.

✱【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
 PCB TOLERANCE:±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.*±5°	PART NO.	TITLE:	
.XX±0.25	X.X*±2°	D-SUB-DMR15PF-E006	HDR15F 铆锁	
.XXX±0.15	X.XX*±1°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olivia	SCALE N:A	SHEET 1/1
MATERILA	— — —	APPD: Ava		
FINISH	— — —			