




SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/0.3A AC;
- 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN;
- 4.CONTACT RESISTANCE: 100m Ω MAX;
- 5.OPERATING TEMPERATURE RANGE: -35°C TO 85°C.

MATERIAL:

- 1.INSULATOR: LCP UL 94V-0 BLACK;
- 2.TERMINAL: COPPER ALLOY;
- 3.METAL FITTINGS: COPPER ALLOY.

PLATING:

- 1.TERMINAL: GOLD PLATING,
NICKEL 50u" MIN. OVER ALL;
- 2.METAL FITTINGS: TIN 100u" MIN. OVER NICKEL
50u"MIN.

Model	PIN	DIM A	DIM B	DIM C
JXT-0.4V08-10PDS	10	4.50	3.40	1.60
JXT-0.4V08-12PDS	12	4.90	3.80	2.00
JXT-0.4V08-16PDS	16	5.70	4.60	2.80
JXT-0.4V08-20PDS	20	6.50	5.40	3.60
JXT-0.4V08-24PDS	24	7.30	6.20	4.40
JXT-0.4V08-30PDS	30	8.50	7.40	5.60
JXT-0.4V08-34PDS	34	9.30	8.20	6.40
JXT-0.4V08-40PDS	40	10.50	9.40	7.60
JXT-0.4V08-50PDS	50	12.50	11.40	9.60

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.25	±1°	PART NO.	TITLE:		
.XX±0.20		JXT-0.4V08-NPDS	BTB P0.40 SOCKET		
.XXX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				