








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Specifications:
Electrical:


- Current Rating
1.5A/contact terminal
- Voltage Rating
30V DC
- Contact Resistance
30 milliohms MAX
- Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- Insulation Resistance:
1000MEGA ohms MIN

Mechanical:

- Connector Mate and Unmate Force
Mate force:3.75kgf(MAX)
Unmate force:1.02kgf(MIN)
- Terminal Retention
1.2kgf(MIN)

Material:

- Housing:
Hing Temperature
Ternmaplastics,
UI 94V-0 PBT White
 - Contact:Copper Alloy C2680
 - Shell: Copper Alloy C2680/SPCC
- Finish:
- Contact: Plated Gold in Mating Area;
Tin On Solder Talls.
 - Shell:
Nickel Plating

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.30	X.*±3°	PART NO. USB-B01	TITLE: USB B/F 90°DIP(弯脚)		
X.X±0.20	X.X*±2°				
X.XX±0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1