




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

SPECIFICATIONS

- 1.CURRENT RATING: 0.3A .
- 2.VOLTAGE RATING 30V AC/DC.
- 3.TEMPERATURE RANGE: -35°C TO $+85^{\circ}\text{C}$
- 4.CONTACT RESISTANCE: 90m Ω MAX.
- 5.INSULATION RESISTANCE: 50 M Ω MIN.
- 6.WITHSTANDING VOLTAGE: 100V AC/MINUTE.



PIN	A	B	C
JXT-10DS-0415	4.6	1.6	1.0
JXT-12DS-0415	5.0	2.0	
JXT-20DS-0415	6.6	3.6	
JXT-24DS-0415	7.4	4.4	1.2
JXT-30DS-0415	8.6	5.6	1.5
JXT-34DS-0415	9.4	6.4	2.3
JXT-40DS-0415	10.6	7.6	3.2
JXT-50DS-0415	12.6	9.6	
JXT-60DS-0415	14.6	11.6	
JXT-70DS-0415	16.6	13.6	
JXT-80DS-0415	18.6	15.6	
JXT-90DS-0415	20.6	17.6	
JXT-100DS-0415	22.6	19.6	

The product is high	H
JXT-NDS-0415	1.45
JXT-NDS-0420	1.95
JXT-NDS-0424	2.40
JXT-NDS-0429	2.90
JXT-NDS-0434	3.40
JXT-NDS-0439	3.90

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
$X \pm 0.50$	$X.^{\circ} \pm 2^{\circ}$	PART NO. JXT-NDS-0415	TITLE: 0.40MM BTB SOCKET		
$X.X \pm 0.35$	$X.X.^{\circ} \pm 1^{\circ}$				
$X.XX \pm 0.25$					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1