








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



备注(NOTE): 1材质:

1.1胶芯:LCP UL94 V-0

1.2端子:(C2680,;镍底,镀金0.5U

1.3外壳:不锈钢304—表面镀镍50U

2.电气特性:

2.1.接触区:接触电阻30mΩMax,
允许10mΩ变化量,

测试条件:20mv,100mA下测量,

2.2.额定电流:最大3A

2.3.额定电压:5V.

2.4.耐电压:100VAC.

2.5.绝缘电阻:至少100兆欧

3.机械性能:


3.1.插入力:0.5-2.0Kg

3.2.拔出力:0.8-2.0Kg

3.3.插拔次数:5000+.

4.工作环境:-20°Cto +85°C

4.1.盐雾测试:24H



USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	PIN NUMBER	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
A5	CC1	.X±0.35	X.*±2°				
A9	VBUS	.XX±0.25		PART NO.	TITLE: USB-type C 6pin 6.8母座直立式贴板成品		
A12	GND	.XXX±0.15		TYPE-C-6PLT-H6.8			
B12	GND	UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
B9	VBUS	MATERILA	---	CHED: Olvia			
B5	CC2	FINISH	---	APPD: Ava			
						SCALE N:A	SHEET 1/1