





DC-018	DC-018-1
 5	 5
 2	 2
 3	 3

SCHEMATIC



Center pin diameter:
 $\phi 2.0$ & $\phi 2.35$ & $\phi 2.5$



Specification:

- Rating : DC 30V 2A;
- Contact resistance: $\leq 50\text{m}\Omega$;
After test: $\leq 100\text{m}\Omega$
- Insulation resistance: $\geq 100\text{M}\Omega$ (500VDC);
After test: $\geq 50\text{M}\Omega$
- Withstand voltage: 500VAC ;
- Insertion and extraction force: 3N~30N;
- life test: 5000cycles MIN.;

PIN	$\phi 2.0$	$\phi 2.35$	$\phi 2.5$
APPD.			

电话 : 0769-82310511-867
 邮箱 : hooya89@hooya.hk
 V: hooya89

					TOLERANCE UNLESS SPECIFIED		3	2019.12.11	增加公头和线路图			XYZ			
							2	2016.6.14	3.3改为2.8			HX			
6	COVER	PBT	1	BLACK	UP TO 5mm:±0.1	ANGULAR ±1°	1	2016.4.25	更新图框			HX			
5	CONTACT FOOT	BRASS	1	Ag-Plated	ABOVE 5mm:±0.2		NO	DATE	REVISIONS			BY	APPD		
4	PIN	BRASS	1	Ni-Plated	TITLE: DC JACK				UNIT : MM	ROHS COMPLIANT	DWN				
3	SPRING	SUS	1	Ag-Plated	MODEL: DC-018-2.0				SCALE: 1:1		CHK'D				
2	FLAT PIECE	BRASS	1	Ag-Plated	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD			
1	HOUSING	PBT	1	BLACK											
NO.	PART	NAME	MATERIAL	QTY	FINISHING								PRO.AGL:	 	REV :A3