







Model No.	PJ-322A	PJ-322A-1
Schematic		

SPECIFICATION

- 1.Rating : DC 30V 0.5A;
- 2.Contact resistance: $\leq 30\text{m}\Omega$;
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V);
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 3-30N;
- 6.life test: 5000 cycles.

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm: ±0.1	ANGULAR							
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
5	RING SPRING ④	PHOSPHOR BRONZE	1	Ag-Plated	TITLE: PHONE JACK				UNIT : MM	ROHS	DWN		
4	RING SPRING ③	PHOSPHOR BRONZE	1	Ag-Plated	MODEL: PJ-322A				SCALE: 1:1	COMPLIANT	CHK'D		
3	TIP SPRING ②	BRASS	1	Ag-Plated	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
2	EARTH SPRING ①	PHOSPHOR BRONZE	1	Ag-Plated					PRO.AGL: 		REV :A0		
1	HOUSING	PBT(UL94V-0)	1										
NO.	PART NAME	MATERIAL	QTY	FINISHING									