



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

1.) MATERIAL:





- 1-1. HOUSING:LCP,UL 94V-0,COLOR:BLACK;
1-2. CONTACT:C2680 T=0.20;
1-3. SHELL:SPCC ,T=0.50;

2.) FINISH:


- 2-1. CONTACT: Au G/F PLATING ON CONTACT AREA,(SEE P/N DESCRIBING) MATTE PURE Sn 50u" Min. PLATING ON SOLDER TAILS
2-2. SHELL: PLATING Ni 50u Min

3.) SPECIFICATIONS:

- 3-1. VOLTAGE RATING: 40V
3-2. CURRENT RATING: 0.5A
3-3. INSULATION RESISTANCE: 100MEG.OHM MIN
3-4. CONTACT RESISTANCE: 10 MILL.OHM MAX
3-5. OPERATION TEMPERATURE: -20°C TO +85°C
3-6. INSERT FORCE: 44.1N MAX
3-7. EXTRACT FORCE: 9.8~39.2N



RECOMMENDED PCB LAYOUT (T:1.60mm)
TOLERANCE UNSPECIFIED ±0.10mm



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.25	.X*±1°	PART NO. HDMI-19PIN-043	TITLE: HDMI		
.XX±0.15	.XX*±0.5°				
.XXX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/2

