


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

- 规格说明:Specifications:
电气特性:Electrical:
1.额定电流:Current Rating
1.0A/contact terminal
2.额定电压:Voltage Rating30V DC
3.接触阻抗>Contact Resistance50 milliohms MAX
4.耐电压:Dielectric Withstanding Voltage:300 V AC AT Sea Level
5.绝缘阻抗:Insulation Resistance: 100MEGA ohms MIN
原材料:Raw material:
1.塑胶:Plastic cement:
High Temperature Thermoplastics, LCP Black
2.端子:Contact:Copper Alloy C2680/C5191
3.外壳:Shell:SPCC/Copper Alloy C2680
电镀:Electroplate:
1.端子:Contact:Plated Gold in Mating Area; Tin On Solder Talls
2.外壳:Shell:
Nickel Plating



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO. MINI-5PTP	TITLE: MINI USB 5P/F SMT B型(0.3T, 0.6#)		
.XX±0.20	X.X°±2°				
.XXX±0.10					
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	---	CHED:	Olvia		
FINISH	---	APPD:	Ava	SCALE N:A	SHEET 1/1