









A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



8					TOLERANCE								
7					UNLESS SPECIFIED								
6	TOP SHELL	SUS	1	Ni-PLATED	UP TO 5mm:±0.1	ANGULAR	1						
5	SHELL	SUS	1	Ni-PLATED	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
4	SPRING	SUS	1		TITLE: USB JACK				UNIT : MM	ROHS COMPLIANT	DWN		
3	SHIELDING PLATE	SUS	1	Ni-PLATED	MODEL: USB-306C-B-SU				SCALE: 1:1		CHK'D		
2	CONTACT	PBS	24	Au/Ni-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD		
1	HOUSING	LCP	1										
NO.	PART NAME	MATERIAL	QTY	FINISHING							PRO.AGL:		REV :A0